


# Band-Master® ATS

## Manual and Pneumatic Tool Accessories

### Accessories



#### 601-400 Foot Pedal Control for 601-106, 601-107, 601-110 and 601-118 Pneumatic Banding Tools

*The 601-400 Foot Pedal Control* frees both hands to help assure more accurate, reliable and faster shield terminations.



#### 601-401 Pneumatic Tool Balancer

*The 601-401 Tool Balancer* for use with pneumatic banding tools 601-104, 601-105, 601-106, 601-107. Load capacity, 1.5 (0.5 kg) to 3.0 Lbs (1.4 kg). Cable length, 6 ft (1.8 m). Reel weight, 1.3 Lbs (0.6 Kg). Pneumatic tool head weight, 2.52 Lbs (1.14 Kg)



#### 600-164 Utility Shears

*The 600-164 Large Broad Utility Shear* for cutting amberstrand® and braided metal shielding also cuts rubber, cable jacketing, cable, plastics and rope. Weight: 0.55 Pounds, Shear Cut Length: 2.000.

#### Recommended AmberStrand® Cutting Procedure

Note: When cutting braid, both metal and especially composite, open cutter blades to allow the full 2" cut. Place braid all the way back onto blades as shown.