


# HIGH-TEMPERATURE TOLERANT ThermaRex HT Series 79




## High-Performance Crimp-Contact Micro-D 797-757 Receptacle Details

### CROSS-SECTIONAL VIEW AND HARDWARE




CONNECTOR SUPPLIED WITH NON-REMOVABLE GUIDE POST FOR BLIND MATE APPLICATION.  
FLOAT MOUNT BUSHING HAS SHELL SIZES "M", "L" & "H" WITH #4-40 UNC-2B THREAD. ALL OTHER SIZES HAVE #2-56 UNC-2B THREAD.

### SHELL SIZES A, B, C, D, E, F, J, K



### SHELL SIZE G






# HIGH-TEMPERATURE TOLERANT ThermaRex HT Series 79



## High-Performance Crimp-Contact Micro-D 797-757 Receptacle Details

### SHELL SIZES H AND L



### SHELL SIZE M

