

SERIES 06


Hold-Down and Release Mechanisms



061-029 Medium-Duty HDRM · Connectorized · Redundant circuit
1000 lb release preload



HOW TO ORDER			
Sample Part No.	061-029	-D	-1450
Basic Part No.	Medium-Duty HDRM, Redundant Circuit		
Connector Options	-D = D38999 (Glenair P/N D38999/24GA35PN. Contact assignment per Table I.) -M = Series 806 Mil-Aero (Glenair P/N 806-020-ME8-4PBA. Contact assignment per Table II. Mates with plug 806-012-ME8-4SBA.)		
Mod Code	-1450 = 80µin (2µm) wire silver plating XL-ETFE Omit for standard MS22759/44 wire		



D Connector option
D38999/24

TECHNICAL DATA	
Tested Capability	
Qualified design based off similarity consult factory for test report	
Electrical Characteristics	
Initiation Circuit Resistance	2.0 Ohms max
DC Insulation Resistance	>2 MΩ at 250 VDC
Qualification Actuation Current	3.5 Amps, < 100 msec
No Fire Current	0.25 Amp for 5 min., all conditions
Physical Characteristics	
Bolt	.190-32 UNJF-3B
Material list	IAW MSFC-STD-3029

TABLE I - 061-029-D	
Pin Assignments for D38999 connector	
Pin	Definition
1	Primary
2	Primary
3	Open (to be populated)
4	Redundant
5	Redundant
6	Open (to be populated)

TABLE II - 061-029-M	
Pin Assignments for Sr. 806 Mil-Aero connector	
Pin	Definition
1	Primary
2	Primary
3	Redundant
4	Redundant

MATERIALS/FINISH

- Housing: Al Alloy / Electroless Nickel IAW AMS-C-26074
- Release Rod, Load Segments: Stainless Steel
- Insulator: Torlon
- Wire: GS22759-44 silver-plated XL-ETFE. Use Mod Code **-1450** for Red Plague resistant 80µin (2µm) Ag plating.

FEATURES AND BENEFITS

- Redundant initiation: 2 initiation points
- Field refurbishable: Initiator can be replaced in less than 15 minutes by trained personnel
- Packaging: External housing typically supplied with two mounting points. Custom housings and mountings available

SERIES 06

Hold-Down and Release Mechanisms



061-029 Medium-Duty HDRM · Connectorized · Redundant circuit
1000 lb release preload

